

Quantec Interface Unit c/w Remote Socket Part No. QT636



Overview

- Allows any device with a normally open or normally closed 6.35mm (1/4 inch) jack plug to be connected to Quantec.
- Particularly suited for use with our NC805MD Portable Movement Detector (n/o operation), QT644 Floor Pressure mat • (n/o operation), QT633 Bed Exit mat (n/c operation) or QT634 Chair Exit Mat (n/c operation).
- Must be wired to a QT602 or QT609 range addressable call point or QT630 dementia care controller.
- When the device connected to the QT636 is operated a call will be generated on the Quantec call system as programmed. •
- Mounts on a standard UK 25mm single gang back box.

UĶ

More Information

Technical Specifications

Quiescent current	1mA.
Alarm current	1mA.
Connections	N-; N+; L+; SW. Wired as a dummy/extender to a QT602 call point, QT609 call point or QT630 dementia care controller.
Onboard 6.35mm Remote Jack Socke	t Yes, can be configured to accept a n/o or n/c jack plug.
Onboard Sounder	No,
Onboard Infrared Receiver	No.
Product dimensions (mm)	87 W x 87 H x 33 D mm. Can be mounted on a standard UK 25mm single gang flush or surface back box.
Construction & finish	Plastic.



T 01942 322744 E sales@c-tec.co.uk

F 01942 829867 W www.c-tec.com

C-TEC, Challenge Way, Martland Park, Wigan, WN5 0LD United Kingdom





IP Rating Weight Operating conditions/temperature

IP20. 68g -5ºC to +40ºC. Max relative humidity: 95%.





